

Boats for the VACO 250

CMi Reference	Description	Type
1800	(10) Large W boats for VACO 250	Tungsten Boat 260W 120A 0.1 mm 
1810	(5) Large W boats for VACO 250	
1801	(10) Small W boats for VACO 250	Tungsten Boat 260W 100A 0.1 mm 
1811	(5) Small W boats for VACO 250	

Materials for the VACO 250

CMi Reference	Material	Quantity
1701	Au : Gold grains	6 grammes
1702	Ag : Silver granulate	around 4 grammes
1703	Al : Aluminum rods	around 8 grammes
1704	Cr : Chromium granulate	around 10 grammes
1705	Cu : Copper rods	around 20 grammes
1706	In : Indium rods	around 25 grammes
1504	Precision tweezers (stainless steel) FC-SA	